

Koch Filter Corporation Filtration Products Crafted with Pride

# **BioMAX**<sup>TM</sup>

A Complete Line of HEPA Filters for Hospital, Commercial and Industrial Applications



- Available in three efficiencies on 0.3 micron size particles: 99.97% and 99.99% HEPA (High Efficiency Particulate Air Filters) 99.999% ULPA (Ultra Low Penetration Air Filters)
- Standard and High Capacity Models
- Multiple Cell Side options
- Factory tested for efficiency and performance

# Koch Filter Corporation...Durable. Reliable. Versatile.

Bulletin No. K-603A

# **BioMAX HEPA Filters**

Koch Filter Corporation BioMAX HEPA Filters are designed to provide the highest level of filtration available for commercial



and industrial applications. They are widely used in hospitals, clean rooms, pharmaceutical plants, and in hundreds of other systems where clean air is critical in the protection of people, processes and equipment.

BioMAX HEPA Filters are constructed using the highest quality components available and are available in efficiencies of 99.97%, 99.99% and 99.999% on 0.3 micron size particles.

Standard construction BioMAX HEPA Filters are manufactured with galvanized steel cell sides (UL Class 1) or particle board cell sides (UL Class 2). Multiple cell side options are also available.

# **BioMAX Performance Testing**

**Prior to shipment**, BioMAX HEPA Filters are tested individually for efficiency utilizing non-toxic polyalphaolefin (PAO) to insure that every filter meets the customer's required efficiency specifications.

Following the individual efficiency test, depending on the acceptance criteria chosen by the customer, BioMAX filters may also be scanned for pinhole leaks with the use of a specialized high intensity light or a custom-built laser photometer.

After testing to the customer's criteria, each filter is certified and labeled with its own serial number. All data is recorded and retained internally.

Penetratio	n:	.025	_%	+
Resistance:		.97	_ IN W.G.	
fest Flowr	ate:	1050		ARELOW
Bize: 24 X 2		4 X 11.6		Fitur can be installed
P/N: 114-703-001				direction
ierial #; 10	0709			
11 11 11 11 11 11 11 11 11 11 11 11 11	1-120	TAS TO PLA	MMABLITY ONLY	

# **BioMAX Construction**

#### Cell Sides -

Standard BioMAX HEPA Filters are constructed with a choice of either 18 gauge galvanized steel or durable particle board cell sides. For more specialized applications, multiple cell side options are available including stainless steel, aluminum, and aluminized steel.

#### High Efficiency Filter Media

BioMAX media is produced from submicron glass fibers formed into a waterresistant, high efficiency, high density wet-laid paper mat. The media is fire retardant to 1000°F (538°C).



BioMAX HEPA filters qualify for the Koch Green Icon

#### Gaskets

Standard BioMAX HEPA Filters are furnished with neoprene gaskets <sup>1</sup>/4" x <sup>11</sup>/<sub>16</sub>". The gasket is installed on the downstream side of the filter to prevent leakage between the filter and the frame upon installation in the filter housing (High temperature silicone and other gasket materials are also available).

#### Rolled Double-Edge Aluminum Separators

Precision-crafted corrugated aluminum separators maintain exact pleat spacing and ensure proper airflow throughout the filter's lifecycle. The leading edge of each separator is rolled over to create a separator that is twice as strong to avoid damage to the air filter media (Vinyl-coated separators are available for applications with corrosive environments).

#### Adhesive Sealant

The media pack in BioMAX HEPA filters is completely sealed to the cell side frame with a specially-designed polyurethane foam bond. As the adhesive cures, the material expands into the media pack eliminating leaks.

# **BioMAX Versatility**

**BioMAX HEPA Filters** are extremely versatile and are used in a wide variety of filtration systems worldwide. In order to meet the wide range of airflow requirements, atmospheric conditions, and pressure drop parameters found in these diverse applications, Koch offers the BioMAX in two media area capacity levels and in multiple construction configurations for specialized applications.

# Two Media Area Capacity Options



# Standard Capacity BioMAX

Standard Capacity BioMAX Filters offer an excellent combination of high efficiency, factory tested performance, and economical initial purchase price.

The filter is designed to operate under normal conditions, with

the 12" deep model capable of maintaining a pressure drop of 1.0" w.g. at airflows up to 260 feet per minute.

Standard Capacity BioMAX Filters are offered with wood or metal cell sides in efficiencies of 99.97%, 99.99%, and 99.999% on 0.3 micron particles.

# **BioMAX Filters for** Specialized Applications



# BioMAX High Temperature HEPA Filters

Several models are available for use in systems with abovenormal operational temperatures.



## BioMAX 95% DOP Filter

Bridges the gap between ASHRAE and HEPA efficiencies.

Contact your Koch Filter Corporation representative for information about other specialized BioMAX models.

## High Capacity BioMAX HC

High Capacity BioMAX HC Filters are designed to operate in applications with higher airflows up to 500 FPM (Feet per Minute). Constructed with approximately 50% more filter media than Standard Capacity Filters, High Capacity BioMAX HC Filters can operate at velocities up to 2000 CFM with only a slight



increase in pressure drop and offer several additional performance advantages:

- Lower average pressure drop at equivalent airflows.
- Can operate at higher airflows with only slight increase in resistance.
- Extended media area means longer service life, fewer filter changes, and reduced maintenance and disposal costs.
- Reduced space requirements for filter banks, fewer filters required.
- Excellent choice for new systems and renovations of existing systems.

High Capacity BioMAX Filters are offered with wood or metal cell sides in efficiencies of 99.97%, 99.99%, and 99.999% on 0.3 micron particles.

#### Optional BioMAX Components and Features

Cell Side Options 18 gauge galvanized steel (standard metal) Particle board (standard wood) 304 Stainless steel 16 gauge galvanized steel Aluminized steel Aluminum Plywood

Separator Options Corrugated aluminum (standard) PVC coated aluminum

Gasket Options Neoprene (standard downstream) Silicone Fiberglass Rope BioMAX are furnished standard with gasket downstream. Also available with gasket on both sides or with no gasket.

Sealant Options Polyurethane Foam (standard) Solid Urethane (optional on some models)

Faceguards Options Expanded galvanized steel Expanded aluminized steel Stainless steel

# Standard Cell Side Configurations (side view)

#### Double Turned Flange





Standard configuration for wood-framed BioMAX Filters. Box style is also available in metal frame.

Some components and cell side configurations are not available on certain BioMax models. Contact your Koch representative for additional information on components, features and cell side configurations



# Koch Filter Corporation Filtration Products Crafted with Pride

# **BioMAX Technical Data**

Size	Capacity	99.97%	99.99%	99.999%
H x W x D (inches)	(CFM)	Initial Pressure Drop	Initial Pressure Drop	Initial Pressure Drop
BIOMAX Standard Capacity				
24 x 24 x 11½	1050	1.0" w.g.	1.0" w.g.	1.1" w.g.
12 x 24 x 11½	525	1.0" w.g.	1.0" w.g.	1.1" w.g.
23% x 23% x 11½	1000	1.0" w.g.	1.0" w.g.	1.1" w.g.
11% x 23% x 11½	475	1.0" w.g.	1.0" w.g.	1.1" w.g.
<b>12 x 12 x 11</b> ½	275	1.0" w.g.	1.0" w.g.	1.1" w.g.
<b>18 x 24 x 11</b> ½	800	1.0" w.g.	1.0" w.g.	1.1" w.g.
<b>24 x 30 x 11</b> ½	1325	1.0" w.g.	1.0" w.g.	1.1" w.g.
<b>30 x 24 x 11</b> ½	1325	1.0" w.g.	1.0" w.g.	1.1" w.g.
8 x 8 x 5%	60	1.0" w.g.	1.0" w.g.	1.1" w.g.
12 x 12 x 5%	140	1.0" w.g.	1.0" w.g.	1.1" w.g.
12 x 24 x 5%	265	1.0" w.g.	1.0" w.g.	1.1" w.g.
18 x 24 x 5%	420	1.0" w.g.	1.0" w.g.	1.1" w.g.
23¾ x 23¾ x 5½	520	1.0" w.g.	1.0" w.g.	1.1" w.g.
24 x 24 x 51/8	550	1.0" w.g.	1.0" w.g.	1.1" w.g.
24 x 30 x 5%	690	1.0" w.g.	1.0" w.g.	1.1" w.g.
24 x 36 x 5%	820	1.0" w.g.	1.0" w.g.	1.1" w.g.
24 x 48 x 5%	1100	1.0" w.g.	1.0" w.g.	1.1" w.g.
24 x 60 x 5%	1365	1.0" w.g.	1.0" w.g.	1.1" w.g.
24 x 72 x 51/8	1640	1.0" w.g.	1.0" w.g.	1.1" w.g.
30 x 24 x 5%	690	1.0" w.g.	1.0" w.g.	1.1" w.g.
30 x 30 x 5%	860	1.0" w.g.	1.0" w.g.	1.1" w.g.
30 x 36 x 5%	1030	1.0" w.g.	1.0" w.g.	1.1" w.g.
30 x 48 x 5%	1365	1.0" w.g.	1.0" w.g.	1.1" w.g.
30 x 60 x 5%	1700	1.0" w.g.	1.0" w.g.	1.1" w.g.
30 x 72 x 5%	2050	1.0" w.g.	1.0" w.g.	1.1" w.g.
36 x 24 x 5%	820	1.0" w.g.	1.0" w.g.	1.1" w.g.
36 x 30 x 5%	1030	1.0" w.g.	1.0" w.g.	1.1" w.g.
36 x 36 x 51/8	1235	1.0" w.g.	1.0" w.g.	1.1" w.g.
<b>36 x 48 x 5</b> <sup>7</sup> / <sub>8</sub>	1640	1.0" w.g.	1.0" w.g.	1.1" w.g.
36 x 60 x 51/8	2050	1.0" w.g.	1.0" w.g.	1.1" w.g.
36 x 72 x 5%	2460	1.0" w.g.	1.0" w.g.	1.1" w.g.
BioMAX HC High Capacity				
<b>24 x 24 x 11</b> ½	2000	1.4" w.g.	1.4" w.g.	1.5" w.g.
<b>12 x 24 x 11</b> ½	1000	1.4" w.g.	1.4" w.g.	1.5" w.g.
23¾ x 23¾ x 11½	1900	1.4" w.g.	1.4" w.g.	1.5" w.g.
11¾ x 23¾ x 11½	925	1.4" w.g.	1.4" w.g.	1.5" w.g.

Additional BioMAX Information 1. Underwriter's Laboratories Classifications: a. Metal framed BioMAX HEPA Filters: UL Class 1. b. Wood framed BioMAX HEPA Filters: UL Class 2.

2. Sizes listed above are actual filter sizes, excluding gaskets.

3. Manufacturing tolerance: +0", -1/8".

4. Install BioMax filters with pleats in vertical position.



**Corporate Offices** 

P.O. Box 3186 • 625 West Hill Street (40208) Louisville, KY 40201 • 502.634.4796 Fax: 502.637.2280 • E mail: info@kochfilter.com www.kochfilter.com



Atlanta, GA • Detroit, MI • East Greenville, PA\* • Houston, TX\* • Indianapolis, IN Kansas City, MO • Louisville, KY\* • Madbury, NH • Nashville, TN • Rancho Cucamonga, CA\*

\*Denotes manufacturing site.

#### © MARCH 2010 KOCH FILTER CORPORATION

Koch Filter Corporation maintains a policy of continuous product research and improvement, and retains the right to change product specification and design without notice.



**Distributed by**